

CEMENT & MORTAR

Cement Flow Table



There are two models of the Cement Flow Table according to ASTM and EN standard. Both are used for determining the consistency of mortar, lime and cement specimens. Also manual and motorized models are available.

The hand operated model is fitted with a hand wheel. The motor operated model is driven by a motor through a mechanical coupling. The number of drops is preset on a counter and the machine stops automatically at the end of the cycle.

EN model, the table is manufactured from stainless steel and has a 300 mm diameter table. The conical mould is made of stainless steel and has dimensions of 100 mm base dia. x 70 mm top dia. x 60 mm height.

ASTM model; the table is manufactured from brass and has 254 mm diameter. The conical mould is made of brass has dimensions of 100 mm base dia. X 70 mm top dia. X 50 mm height.

All models are supplied complete with flow mould and tamper.

You May Also Be Interested In



**Electronic Blaine Air
Permeability Apparatus**

PCE-153



**Automatic Cement Compression
& Flexure Testing Machines**

PCE-CF.CT



**Three Gang Mould,
40.1x40x160mm**

PCE-171

Review Product on Our Website

To access up-to-date technical details, images, and documentation for this product, you can scan the QR code on the right using your smartphone camera or visit our website directly.

